

## SCANITY Maximum Scanning Speeds

Mode	SCANITY			
	Speed A	Speed B	Speed C	Speed D
<b>35 mm 4 Perf</b>				
4k	15	12	9	6
2k	25	20	15	10
1k	44	36	28	18
.5k	66	55	44	28
.25k	96	80	66	44
<b>35 mm 3 Perf</b>				
4k	20	16	12	8
2k	33	27	20	13
1k	59	48	37	24
.5k	88	73	59	37
.25k	128	107	88	59
<b>35 mm 2 Perf</b>				
4k	30	24	18	12
2k	50	40	30	20
1k	88	72	56	36
.5k	132	110	88	56
.25k	132	132	110	72
<b>35 mm 8 Perf</b>				
4k	8	6	5	3
2k	13	10	8	5
1k	22	18	14	9
.5k	33	28	22	14
.25k	48	40	33	22
<b>16mm</b>				
4k	18	15	10	10
2k	30	25	18	15
1k	50	37	30	18
.5k	90	70	50	30
.25k	137	90	70	50

**Note:**

Record speed may be less and depends on the performance of the data receiving device. In play, monitored frames may be dropped from a certain speed onwards in the GUI monitoring only. 4k only speeds do not apply to SCANITY 2K versions. More (lower) speeds can be selected in the GUI.