

SCANITY Maximum Scanning Speeds

Mode	SCANITY			
	Speed A	Speed B	Speed C	Speed D
35 mm 4 Perf				
4k	15	12	9	6
2k	25	20	15	10
1k	44	36	28	18
.5k	66	55	44	28
.25k	96	80	66	44
35 mm 3 Perf				
4k	20	16	12	8
2k	33	27	20	13
1k	59	48	37	24
.5k	88	73	59	37
.25k	128	107	88	59
35 mm 2 Perf				
4k	30	24	18	12
2k	50	40	30	20
1k	88	72	56	36
.5k	132	110	88	56
.25k	132	132	110	72
35 mm 8 Perf				
4k	8	6	5	3
2k	13	10	8	5
1k	22	18	14	9
.5k	33	28	22	14
.25k	48	40	33	22
16mm				
4k	18	15	10	10
2k	30	25	18	15
1k	50	37	30	18
.5k	90	70	50	30
.25k	137	90	70	50

Note:

Record speed may be less and depends on the performance of the data receiving device. In play, monitored frames may be dropped from a certain speed onwards in the GUI monitoring only.

4k only speeds do not apply to SCANITY 2K versions.

More (lower) speeds can be selected in the GUI.